PAPERS V5 FOILS

What are the main differences between Bausch papers and foils?

ARTICULATING PAPERS







200µ

100μ

40μ

- Marks under pressure with progressive color transfer
- Large contact markings
- Illustrates different pressure forces
- Excels on wet surfaces
- Best for checking static occlusion

BOTH TYPES
AVAILABLE IN
ADDITIONAL SHAPES,
THICKNESSES,
AND/OR COLORS!







12μ Arti-Fol® Film

ARTICULATING FOILS

Practical for both static and dynamic occlusion



- Precisely shows high-spots
- Pin-point contact markings
 - Tear-Resistant

More info at

BAUSCHPAPER.COM